



Main

Range	Exiway
Product name	Exiway Smartbeam DiCube
Product or component type	Emergency light
Device application	Lighting
Function	Addressable
Supply	Non-maintained Maintained
Number of batteries	1 x 6.4 V 1.5 Ah LiFePO4
Light source	1 x LED 10 W

Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Power consumption in VA	4.6 VA non-maintained 8.7 VA maintained
Power consumption in W	3.5 W maintained 0.52 W non-maintained
Electrical insulation class	Class II
Communication port protocol	DALI
Bulb lifespan	100000 H
Function available	Automatic addressing of emergency lighting by means of control unit
Autonomy	3 h
Charging time	12 H
Luminous flux	220 Lm
Illuminance	0.5 Lux
Material	Thermoplastic self-extinguishing
Device mounting	Flush false ceiling
Height	Driver: 55.8 mm
Width	Driver: 256.6 mm
Depth	Driver: 23.8 mm Light fitting: 31.5 mm
Diameter	90 Mm light fitting:
Net weight	335 G

Environment

IP degree of protection	Light fitting: IP42 Driver: IP20
IK degree of protection	IK04
Ambient air temperature for operation	0...40 °C
Flame retardance	V2
Fire resistance	850 °C
Product certifications	ENEC CE
Standards	EN 60598-1 EN 62034 UL 94 EN 60598-2-22 EN 62471: group 1 EN 60695-2-10 IEC 62386-202 IEC 62386-102

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**