

Product data sheet

Characteristics

PBPEDU5B100COOS4430M4

Busway Circuit Breaker Plug-in Unit 30A

415/240V 5B 3FT CORD IEC 3P4W W/METER

Main

Product or component type	Plug-in unit
Range of product	Powerbus

Complementary

Line Rated Current	100 A
System Voltage	240/415 V AC
Box number	5B L1 + N + L2 + N + L3
Phase	3 phases
Wiring configuration	4-wire (200 percent neutral)
Circuit breaker name	EDU Breaker, 30 A AMP, 3 pole Number of Breakers 1 breaker
Provided equipment	Meter PM5350
Cable length	3 ft drop cable
Connector type	IEC connector 3P 4 ways-wire with grounding terminal

Environment

NEMA degree of protection	NEMA 1
IP degree of protection	IP40

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.