

Overview

Model Name	APC Essential SurgeArrest 6 Outlet 3 Foot Cord Dual Pack 120V
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Number of Outlets	6
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Power	1200 W
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	3 feet (0.91 meters)
Maximum Input Current	15 A

Surge Protection and Filtering

Surge energy rating	540 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	40.0 dB
Peak Current Normal Mode	12 kA
Peak Current Common Mode	24.0 kA
NM Surge Response Time (ns)	1.0 NS
Let Through Voltage Rating	500

Physical

Net Weight	0.83 lbs (0.38 kg)
Maximum Height	11.02 inches (280.0 mm)
Maximum Width	2.05 inches (52.0 mm)
Maximum Depth	1.18 inches (30.0 mm)
Shipping Weight	1.79 lbs (0.81 kg)
Shipping Height	11.42 inches (290.0 mm)
Shipping Width	4.13 inches (105.0 mm)
Shipping Depth	2.76 inches (70.0 mm)
Master Carton Units	6.0
Master Carton Dimensions (Length x Width x Height)	13.94 x 12.36 x 7.09 inches
Master Carton Weight	5.42 kg
SCC Codes	1073130433661 4

Color	Black , Grey
Units per Pallet	216.0

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	MET Canada , MET USA , UL 1363 , UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$50000
UL 1449 TVSS Rating	500

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs