



Overview

Model Name	APC Home Office SurgeArrest 12 Outlets, 120V
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Number of Outlets	12
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	1.83 meters
Maximum Input Current	15 A

Surge Protection and Filtering

Surge energy rating	2160 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	40.0 dB
Peak Current Normal Mode	28 kA
Peak Current Common Mode	56.0 kA
NM Surge Response Time (ns)	1.0 NS
Let Through Voltage Rating	400

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Physical

Net Weight	0.67 kg
Maximum Height	30.0 mm
Maximum Width	77.0 mm
Maximum Depth	307.0 mm
Shipping Weight	0.77 kg
Shipping Height	48.0 mm
Shipping Width	145.0 mm
Shipping Depth	335.0 mm
Master Carton Units	6.0
Master Carton Dimensions (Length x Width x Height)	13.78 x 6.3 x 12.6 inches
Master Carton Weight	5.01 kg
SCC Codes	1073130433594 5
Color	Black
Units per Pallet	324.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-15000 meters

Conformance

Approvals	MET Canada , MET USA , UL 1363 , UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$150000

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs