

PHD36150GU44X

Busway I-Line Breaker Plug-in Unit, 150A,H-Frame, Micrologic 6.2A, 14kA-600V, 3W



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 6076.00 USD

Main

Product or component type	Plug-in unit
Range of product	I-Line
Circuit breaker type	H-frame
Trip unit technology	Electronic, ammeter, Micrologic 6.2 A, LSIG

Complementary

Protection type	Circuit breaker
Mounting mode	Plug-in
Line Rated Current	150 A
System Voltage	600 V AC
Phase	3 phases
Poles description	3P
[Ics] rated service short-circuit breaking capacity	80 %
Wiring configuration	3-wire (integral ground bus)
Breaking capacity	18 kA at 480 V AC 25 kA at 240 V AC 14 kA at 600 V AC
AWG gauge	AWG 8...AWG 3/0 1 cable(s) phase and neutral AWG 6...AWG 2/0 1 cable(s) ground
Depth	9.13 in (232 mm)
Height	8.5 in (216 mm)
Width	21.69 in (551 mm)

Environment

Product certifications	UL listed file E22182 CSA C22.2 No 27
Standards	UL 857

Ordering and shipping details

Category	20182 - PFA / PHD C/B PLUGS
Discount Schedule	PE7
Nbr. of units in pkg.	1
Package weight(Lbs)	32
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : Commercialised