

PJD36250GM54

Busway I-Line Breaker Plug-in Unit, 250A, J-Frame, Therm-Mag, 14kA-600V, 3W,IP54



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 7337.00 USD

Main

Product or component type	Plug-in unit
Range of product	I-Line
Circuit breaker type	J-frame
Trip unit technology	Thermal-magnetic

Complementary

Protection type	Circuit breaker
Mounting mode	Plug-in
Line Rated Current	250 A
System Voltage	600 V AC
Phase	3 phases
Poles description	3P
[Ics] rated service short-circuit breaking capacity	80 %
Wiring configuration	3-wire (integral ground bus)
Breaking capacity	18 kA at 480 V AC 25 kA at 240 V AC 14 kA at 600 V AC
AWG gauge	AWG 6...AWG 2/0 1 cable(s) ground AWG 3/0...350 kcmil 1 cable(s) phase and neutral
Depth	9.13 in (232 mm)
Height	8.5 in (216 mm)
Width	21.69 in (551 mm)

Environment

Product certifications	UL listed file E22182 CSA C22.2 No 27
Standards	IEC 60529 UL 857
IP degree of protection	IP54

Ordering and shipping details

Category	20185 - PJD C/B PLUGS
Discount Schedule	PE7
Nbr. of units in pkg.	1
Package weight(Lbs)	32
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**