

# PJL36250GU44XM54

Busway I-Line Breaker Plug-in Unit, 250A, J-Frame, Micrologic 6.2A, 50kA-600V, 3W, IP54



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 18284.00 USD

## Main

Product or component type	Plug-in unit
Range of product	I-Line
Circuit breaker type	J-frame
Trip unit technology	Electronic, ammeter, Micrologic 6.2 A, LSIG

## Complementary

Protection type	Circuit breaker
Mounting mode	Plug-in
Line Rated Current	250 A
System Voltage	600 V AC
Phase	3 phases
Poles description	3P
[Ics] rated service short-circuit breaking capacity	80 %
Wiring configuration	3-wire (integral ground bus)
Breaking capacity	125 kA at 240 V AC 100 kA at 480 V AC 50 kA at 600 V AC
AWG gauge	AWG 6...AWG 2/0 1 cable(s) ground AWG 3/0...350 kcmil 1 cable(s) phase and neutral
Depth	9.13 in (232 mm)
Height	8.5 in (216 mm)
Width	21.69 in (551 mm)

## Environment

Product certifications	UL listed file E22182 CSA C22.2 No 27
Standards	IEC 60529 UL 857
IP degree of protection	IP54

## Ordering and shipping details

Category	20185 - PJD C/B PLUGS
Discount Schedule	PE7
Nbr. of units in pkg.	1
Package weight(Lbs)	32
Returnability	N

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**