

PK18GTAL

LOAD CENTER GROUND BAR KIT QO +OPTIONS



Product availability: Stock - Normally stocked in distribution facility

Price*: 37.80 USD



Main

Range of product	QO
Product or component type	Load Center Grounding Bar Assembly

Complementary

Number of connectors	19
AWG gauge	AWG 14...AWG 4 copper AWG 12...AWG 4 aluminium AWG 4...AWG 1 aluminium/copper
Provided equipment	2 QO 1 screw
Bar length	8.82 In (224 mm)
Maximum length of segment	3.15 In (80 mm)
Device mounting	Mounting holes back of enclosure
Tightening torque	20 Lbf.In (2.26 N.m) AWG 14...AWG 10) 20 Lbf.In (2.26 N.m) AWG 12...AWG 10) 25 Lbf.In (2.82 N.m) AWG 8) 35 Lbf.In (3.95 N.m) AWG 6...AWG 4) 25 Lbf.In (2.82 N.m) AWG 14...AWG 12) 25 Lbf.In (2.82 N.m) AWG 12...AWG 10)

Ordering and shipping details

Category	00102 - QO LC ACCESSORIES
Discount Schedule	DE3A
GTIN	00785901440888
Package weight(Lbs)	0.37 Lb(US) (0.17 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive-harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**