



Main

Range	PratiKa
Product or component type	Socket
Device short name	PratiKa socket
Plug, socket category	Low voltage
Poles description	3P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Wall-mounted
Plug, socket, control station shape	Angled
[In] rated current	16 A
[Ue] rated operational voltage	480...500 V
Network frequency	50/60 Hz
Ground lug clockwise position	7 h
Plug, socket material	Self-extinguishing engineering polymer housing :
Contacts material	Brass sleeves :
Connections - terminals	Fast connection
Cable cross section	1...2.5 mm ²
Cable outer diameter	21 mm
Thread type	M25
Product weight	0.22 kg
Height	131 mm
Width	80 mm
Depth	126 mm
Colour	Grey (RAL 7035)
Voltage colour	Black

Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	750 °C conforming to IEC 60695-2-1
Relative humidity	50 % (40 °C) 70 % (30 °C) 90 % (20 °C)
Ambient air temperature for operation	35 °C (86400 s)

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**