



Main

Range	PratiKa
Product or component type	Socket
Device short name	PratiKa socket
Plug, socket category	Low voltage
Poles description	2P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Wall-mounted
Plug, socket, control station shape	Angled
[In] rated current	32 A
[Ue] rated operational voltage	100...130 V
Network frequency	50/60 Hz
Ground lug clockwise position	4 h
Plug, socket material	Self-extinguishing engineering polymer housing :
Contacts material	Brass sleeves :
Connections - terminals	Fast connection
Cable cross section	2.5...6 mm ²
Cable outer diameter	21 mm
Thread type	M25
Product weight	0.28 kg
Height	160 mm
Width	106 mm
Depth	145 mm
Colour	Grey (RAL 7035)
Voltage colour	Yellow

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	750 °C conforming to IEC 60695-2-1
Relative humidity	50 % (40 °C) 70 % (30 °C) 90 % (20 °C)
Ambient air temperature for operation	35 °C (86400 s)

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**