



Overview

Model Name	APC Essential SurgeArrest 1 Outlet 230V, 2 Port USB Charger, France
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Belgium , Czech Republic , France , Poland , Slovakia (Slovak Republic)

Output

Number of Outlets	1
Receptacle Style	France/Belgium

Input

Nominal Input Voltage	230V
Input Frequency	50 Hz +/- 5 Hz
Input Connections	French/Belgian
Maximum Input Current	16 A

Surge Protection and Filtering

Surge energy rating	918 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	30.0 dB
Peak Current Normal Mode	12 kA
Peak Current Common Mode	24.0 kA
NM Surge Response Time (ns)	1.0 NS

Physical

Net Weight	0.16 kg
Maximum Height	100.0 mm
Maximum Width	63.0 mm
Maximum Depth	41.0 mm
Shipping Weight	0.23 kg
Shipping Height	88.0 mm
Shipping Width	70.0 mm
Shipping Depth	106.0 mm
Master Carton Units	12.0
Master Carton Dimensions (Length x Width x Height)	12.01 x 11.26 x 5.26 inches
Master Carton Weight	3.0 kg
SCC Codes	1073130433474 0

Color	White
Units per Pallet	1008.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-5 - 40 °C
Storage Relative Humidity	0 - 95% non-condensing %
Storage Elevation	0-4500 meters

Conformance

Approvals	CE
Standard warranty	Lifetime (European Union countries only)
Equipment protection policy	Lifetime : 50000 Euros

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs