



Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	336 Mm
Height	600 Mm
Depth	143 Mm
Number of 18 mm modules per row	13
Number of horizontal rows	3
Electrical insulation class	Class II Double insulation
Provided equipment	1 x identification label 1 x marking kit 1 x blanking plate strip
Type of front cover	Transparent

Complementary

Enclosure mounting	Surface
9 mm pitches	26
Total number of 18 mm modules	39
Power dissipation in W	45 W
[In] rated current	90 A
Type of rail	DIN
Cable entry	Trunking Cut-out plates Removable plates Cable or tube
Enclosure material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Door: smoked
Targeted country	Italy

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Fire resistance	Back part: 650 °C conforming to IEC 60695-2-1 Front face: 650 °C conforming to IEC 60695-2-1 Door: 650 °C conforming to IEC 60695-2-1
IP degree of protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
IK degree of protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**