



Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	550 Mm
Height	750 Mm
Depth	173 Mm
Number of 18 mm modules per row	24
Number of horizontal rows	4
Electrical insulation class	Class II Double insulation
Provided equipment	1 x identification label 1 x marking kit 1 x blanking plate strip
Type of front cover	Customizable Transparent

Complementary

Enclosure mounting	Surface
9 mm pitches	48
Total number of 18 mm modules	96
Power dissipation in W	87 W
[In] rated current	160 A
Type of rail	Multifix
Cable entry	Cable or tube Trunking Removable plates Cut-out plates
Enclosure material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal Door: glass Door: metal
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004) Door: transparent
Targeted country	Italy

Environment

Fire resistance	Back part: 650 °C Front face: 650 °C Door: 650 °C
IP degree of protection	IP30 without door IP40 with door
IK degree of protection	IK08 without door IK09 with door
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**