



Main

| | |
|---------------------------------|---|
| Range | Pragma |
| Product or component type | Enclosure |
| Enclosure type | Distribution enclosure |
| Width | 610 Mm |
| Height | 780 Mm wall: 810 Mm outside: |
| Depth | 95 Mm wall: 55 Mm outside: |
| Number of 18 mm modules per row | 24 |
| Number of horizontal rows | 4 |
| Electrical insulation class | Class II Double insulation |
| Provided equipment | 2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip |
| Type of front cover | Opaque |

Complementary

| | |
|-------------------------------|--|
| Enclosure mounting | Flush |
| 9 mm pitches | 48 |
| Total number of 18 mm modules | 96 |
| Power dissipation in W | 110 W |
| [In] rated current | 160 A |
| [Ui] rated insulation voltage | 800 V |
| Type of rail | Multifix |
| Cable entry | Cable or tube Side pre-cutouts Removable plates |
| Number of terminal blocks | 1 earth (Quick) with 32 outgoing 1 neutral (Quick) with 35 outgoing |
| Distribution block outgoing | 1 x 50 mm ² for earth 3 x 25 mm ² for earth 28 x 6 mm ² for earth 1 x 50 mm ² for neutral 28 x 6 mm ² for neutral 6 x 25 mm ² for neutral |

| | |
|--------------------|--|
| Enclosure material | Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal Door: glass Door: metal |
| Colour | Door: white (RAL 9016) Enclosure: white (RAL 9016) Front face: grey (RAL 7004) |

Environment

| | |
|---------------------------------------|---|
| Fire resistance | Back part: 650 °C Front face: 650 °C Door: 650 °C |
| IP degree of protection | IP30 without door IP40 with door |
| IK degree of protection | IK08 without door IK09 with door |
| Overvoltage category | II |
| Ambient air temperature for operation | -25...60 °C |
| Standards | IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3 |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**