



Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	570 Mm wall: 610 Mm outside:
Height	930 Mm wall: 960 Mm outside:
Depth	30 Mm outside: 95 Mm wall:
Number of 18 mm modules per row	24
Number of horizontal rows	5
Electrical insulation class	Class II Double insulation
Provided equipment	1 x identification label 1 x marking kit 1 x terminal block 1 x blanking plate strip

Complementary

Enclosure mounting	Flush
9 mm pitches	48
Total number of 18 mm modules	120
Power dissipation in W	133 W
[In] rated current	160 A
[Ui] rated insulation voltage	800 V
Type of rail	Multifix
Cable entry	Cable or tube Removable plates Side pre-cutouts
Number of terminal blocks	1 earth (Quick) with 32 outgoers
Distribution block outgoers	1 x 50 mm ² for earth 3 x 25 mm ² for earth 28 x 6 mm ² for earth
Enclosure material	Back part: technoplastic Front face: technoplastic Back part: metal Front face: metal
Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004)
Targeted country	Denmark

Environment

Fire resistance	Back part: 650 °C conforming to IEC 60695-2-1 Front face: 650 °C conforming to IEC 60695-2-1
IP degree of protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
IK degree of protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	EN 60695-2-11 IEC 60439-3 IEC 60947-7-1 EN 60439-3 IEC 62262 IEC 60695-2-11 IEC 60529

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. - Block**