



Commercial status

End of Commercialisation :

⚠ End of Commercialisation

Main

| | |
|---------------------------------|---|
| Range | Pragma |
| Product or component type | Enclosure |
| Enclosure type | Distribution enclosure |
| Width | 426 Mm |
| Height | 750 Mm |
| Depth | 125 Mm |
| Number of 18 mm modules per row | 18 |
| Number of horizontal rows | 4 |
| Electrical insulation class | Class II Double insulation |
| Provided equipment | 2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip |

Complementary

| | |
|-------------------------------|--|
| Enclosure mounting | Surface |
| 9 mm pitches | 36 |
| Total number of 18 mm modules | 36 |
| Power dissipation in W | 64 W |
| [In] rated current | 125 A |
| Type of rail | DIN |
| Cable entry | Cut-out plates Cable or tube Trunking Removable plates |
| Number of terminal blocks | 1 earth (Quick) with 30 outgoers 1 neutral (Quick) with 28 outgoers |
| Distribution block outgoers | 1 x 25 mm ² for earth 1 x 50 mm ² for earth 28 x 6 mm ² for earth 3 x 25 mm ² for neutral 1 x 50 mm ² for neutral 24 x 6 mm ² for neutral |
| Enclosure material | Back part: technoplastic Front face: technoplastic |
| Colour | Enclosure: white (RAL 9016) |
| Targeted country | Portugal |

Environment

| | |
|---------------------------------------|---|
| Fire resistance | Back part: 750 °C conforming to IEC 60695-2-1 Front face: 750 °C conforming to IEC 60695-2-1 |
| IP degree of protection | IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529 |
| IK degree of protection | IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262 |
| Overvoltage category | II |
| Ambient air temperature for operation | -25...60 °C |
| Standards | IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3 |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **End of commerc. - Block**