



Main

Range	Pragma
Product or component type	Door
Accessory / separate part category	Enclosure accessories

Complementary

Enclosure mounting	Flush Surface
Key number	Number to be stated
Type of front cover	Smoked
Door opening side	Right or left
Number of horizontal rows	2
9 mm pitches	36
Number of 18 mm modules per row	18
Total number of 18 mm modules	36
Enclosure/cubicle description	Surface mounting Flush mounting
Enclosure material	Technoplastic
Width	426 mm
Height	450 mm
Depth	20 mm
Colour	Smoked

Environment

Fire resistance	750 °C
Standards	IEC 60439-3
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN/IEC 62262
Ambient air temperature for operation	-25...60 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**