

PTMJ36350GV

Busway I-Line Circuit Breaker Plug-in Unit, 350A,
M-Frame, 25kA-600V, 3W, Vert



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 17918.00 USD

Main

Product or component type	Plug-in unit
Range of product	I-Line
Circuit breaker type	M-frame
Trip unit technology	Electronic, basic, ET 1.0, LI

Complementary

Protection type	Circuit breaker
Mounting mode	Bolt-on
Line Rated Current	350 A
System Voltage	600 V AC
Phase	3 phases
Poles description	3P
[Ics] rated service short-circuit breaking capacity	80 %
Wiring configuration	3-wire (integral ground bus)
Breaking capacity	65 kA at 480 V AC 25 kA at 600 V AC 100 kA at 240 V AC
AWG gauge	AWG 3/0...500 kcmil 3 cable(s) phase and neutral AWG 6...300 kcmil 4 cable(s) ground
Depth	514 mm
Height	1174 mm
Width	584 mm
Condition of use	Vertical installation

Environment

Product certifications	UL listed file E22182 CSA C22.2 No 27
Standards	UL 857

Ordering and shipping details

Category	20192 - PBMH/PTMH C/B PLUGS
Discount Schedule	PE7
Nbr. of units in pkg.	1
Package weight(Lbs)	284
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric Declaration Of Conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**