

# Product data sheet

## Characteristics

# QO112M100I

## LOAD CENTER QO REPLACEMENT INTERIOR



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 296.00 USD



### Main

Product or component type	Load Center Interior
Range of product	QO
Load center type	Main breaker
Line Rated Current	100 A
Number of spaces	12
Short-circuit current	22 kA
Number of circuits	12
Number of tandem circuit breakers	0
Phase	1 phase
System Voltage	120/240 V AC

### Complementary

Device composition	Grounding bar (ordered separately)
Material	Tin plated copper busbar
Product certifications	UL listed

### Ordering and shipping details

Category	00199 - DE5 MISC. SERVICE PARTS
Discount Schedule	DE5
GTIN	00785901438625
Nbr. of units in pkg.	1
Package weight(Lbs)	10
Returnability	N
Country of origin	US

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	<b>Commercialised</b>
-----------------------	-----------------------