

Product data sheet

Characteristics

QO12030M150RB

QO LoadCenter, Main Breaker, 150A, 1PH-3W, 20SP, NEMA 3R



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility

Price*: 953.00 USD



Main

Product or component type	Load Center
Range of product	QO
Load center type	Main breaker
Line Rated Current	150 A
Number of spaces	20
Short-circuit current	22 kA
Number of circuits	30
Number of tandem circuit breakers	10
Phase	1 phase
System Voltage	120/240 V AC

Complementary

AWG gauge	AWG 4...250 kcmil (aluminium/copper)
NEMA degree of protection	NEMA 3R outdoor
Cover type	Surface cover
Electrical connection	Lugs
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated copper busbar
Enclosure material	Welded galvanized steel
Surface finish	Baked enamel grey
Box number	5R
Product certifications	UL listed
Height	661 mm
Width	14.76 in (375 mm)

Ordering and shipping details

Category	00002 - QO 1PH LC,12-42 CKT,NEMA3R
Discount Schedule	DE3A
GTIN	00785901867968
Nbr. of units in pkg.	1
Package weight(Lbs)	29.93
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1248 - Schneider Electric declaration of conformity Schneider-Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**