

Product data sheet

Characteristics

QO130L200PWG

QO LoadCenter, Main Lugs, 200A, 1PH-3W, 30SP, NEMA 3R, Wide Gutter, PON



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 750.00 USD



Main

Product or component type	Load Center
Range of product	QO
Load center type	Main lugs
Line Rated Current	200 A
Number of spaces	30
Short-circuit current	65 kA
Number of circuits	30
Number of tandem circuit breakers	0
Phase	1 phase


Complementary

AWG gauge	AWG 6...250 kcmil (aluminium/copper)
NEMA degree of protection	NEMA 1 indoor
Cover type	Order separately
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated copper busbar
Enclosure material	Welded sheet steel
Surface finish	Baked enamel grey
Box number	9
Product certifications	UL listed
Height	29.84 in (758 mm)
Width	14.25 in (362 mm)

Ordering and shipping details

Category	10003 - QO PON 1PH LC,12-60 CKT, ML N1
Discount Schedule	DE3A
GTIN	00785901136118
Nbr. of units in pkg.	1
Package weight(Lbs)	22.600000000000001
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1248 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Product Life Status : **Commercialised**