

# Product data sheet

## Characteristics

# QO140L200GRB

QO Load Center, main lug, 200 A, 1 PH, 3 wire,  
40 SP, N3R, gnd bar



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility

Price\*: 971.00 USD



### Main

Product or component type	Load Center
Range of product	QO
Load center type	Main lugs
Line Rated Current	200 A
Number of spaces	40
Short-circuit current	65 kA
Number of circuits	40
Number of tandem circuit breakers	0
Phase	1 phase
System Voltage	120/240 V AC

### Complementary

AWG gauge	AWG 6...250 kcmil (aluminium/copper)
NEMA degree of protection	NEMA 3R outdoor
Cover type	Surface cover
Electrical connection	Lugs
Device composition	Grounding bar included (not installed)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated copper busbar
Enclosure material	Welded galvanized steel
Surface finish	Baked enamel grey
Box number	7R
Product certifications	UL listed
Height	858 mm
Width	14.76 in (375 mm)

## Ordering and shipping details

Category	00002 - QO 1PH LC,12-42 CKT,NEMA3R
Discount Schedule	DE3A
GTIN	00785901747437
Nbr. of units in pkg.	1
Package weight(Lbs)	38.450000000000003
Returnability	Y
Country of origin	US

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1248 - Schneider Electric declaration of conformity <a href="#">Schneider-Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**