

# Product data sheet

## Characteristics

# QO330L200GLN

Load center, QO, 3 phase, 30 spaces, 30 circuits, 200A fixed main lugs, NEMA1, grnd bar, no neutral, UL



by Schneider Electric

Price\*: 620.00 USD



## Commercial status

This Product is Obsolete :

⚠ This Product is Obsolete

## Main

Range of product	QO
Product or component type	Load Center
Cover type	Order separately

## Complementary

Tightening torque	Cover 20 lb.in
Load center type	Main lugs
Line Rated Current	200 A
Number of spaces	30
Short-circuit current	65 KA
Number of circuits	30
Number of tandem circuit breakers	0
Phase	3 phase
[Ue] rated operational voltage	208Y/120 V AC 240/120 V delta AC 240 V delta AC
AWG gauge	AWG 6...250 kcmil aluminium/copper
Electrical connection	Lugs
Device composition	Grounding bar included (not installed)
Electrical connection	Lugs
Wiring configuration	4-wire 3-wire
Material	Tin plated copper busbar
Enclosure material	Welded sheet steel
Surface finish	Baked enamel Gray
Box number	9

Maximum Height	29.84 In (758 mm)
Maximum Width	14.25 In (362 mm)

### Environment

NEMA degree of protection	NEMA 1 indoor
Ambient air temperature for operation	23 °F (-5 °C) 104 °F (40 °C)
Product certifications	UL Listed

### Ordering and shipping details

Category	00166-DE3 MISC
Discount Schedule	DE3
Package weight(Lbs)	5.00 Lb(US) (2.268 kg)
Returnability	Yes

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commercialisation**