

Product data sheet

Characteristics

QO330M150I


LOAD Center QO RPLCMT INT LESS MIB



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 596.00 USD



Main

Product or component type	Load Center Interior
Range of product	QO
Load center type	Main breaker
Line Rated Current	150 A
Number of spaces	30
Short-circuit current	25 kA
Number of circuits	30
Number of tandem circuit breakers	0
Phase	3 phases
System Voltage	208Y/120 V AC 240/120 V delta AC 240 V delta AC

Complementary

Device composition	Grounding bar (ordered separately)
Material	Tin plated copper busbar
Product certifications	UL listed

Ordering and shipping details

Category	00199 - DE5 MISC. SERVICE PARTS
Discount Schedule	DE5
Nbr. of units in pkg.	1
Package weight(Lbs)	10
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	-----------------------