

Product data sheet

Characteristics

QO330MQ125RB

LOAD Center QO RB MB 125A 3PH 30 CIRCUIT



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility

Price*: 2147.00 USD



Main

Product or component type	Load Center
Range of product	QO
Load center type	Main breaker
Line Rated Current	125 A
Number of spaces	30
Short-circuit current	25 kA
Number of circuits	30
Number of tandem circuit breakers	0
Phase	3 phases
System Voltage	208Y/120 V AC 240/120 V delta AC 240 V delta AC

Complementary

AWG gauge	AWG 4...300 kcmil (aluminium/copper)
NEMA degree of protection	NEMA 3R outdoor
Cover type	Surface cover
Electrical connection	Lugs
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire 4-wire
Material	Tin plated copper busbar
Enclosure material	Welded galvanized steel
Surface finish	Baked enamel grey
Box number	14R
Product certifications	UL listed
Height	39.37 in (1000 mm)
Width	14.76 in (375 mm)

Ordering and shipping details

Category	00017 - QO 3PH LOAD CENTER,OUTDOOR
Discount Schedule	DE3
GTIN	00785901290599
Nbr. of units in pkg.	1
Package weight(Lbs)	45.899999999999999
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1411 - Schneider Electric declaration of conformity Schneider-Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**