

Product data sheet

Characteristics

QO403L100S

QO LoadCenter, Main Lug, 100A, 3PH, 3 SP, NEMA 1, Surface Cover, CSA/UL



Product availability: Stock - Normally stocked in distribution facility

Price*: 143.00 USD



Main

Product or component type	Load Center
Range of product	QO
Load center type	Main lugs
Line Rated Current	100 A
Number of spaces	3
Short-circuit current	65 kA
Number of circuits	3
Number of tandem circuit breakers	0
Phase	3 phases
System Voltage	208Y/120 V AC 240/120 V delta AC 240 V delta AC

Complementary


AWG gauge	AWG 10...AWG 6 (copper)
NEMA degree of protection	NEMA 1 indoor
Cover type	Surface cover
Electrical connection	Lugs
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire 4-wire
Material	Tin plated copper busbar
Enclosure material	Welded sheet steel
Surface finish	Baked enamel grey
Product certifications	CSA
Height	12.99 in (330 mm)

Width	5.75 in (146 mm)
Depth	3.31 in (84 mm)

Ordering and shipping details

Category	00158 - CANADIAN 3-PH LOAD CENTERS
Discount Schedule	DE3
GTIN	00785901207757
Nbr. of units in pkg.	1
Package weight(Lbs)	5.8200000000000003
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1248 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	-----------------------