

# Product data sheet

## Characteristics

# QOC24US

Cover, QO, load center, 24 circuits, surface



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility

Price\*: 37.70 USD



### Main

Range of product	QO
Product or component type	Load Center Cover

### Complementary

Device mounting	Surface
Cover type	Surface cover
Product compatibility	For indoor load center
Maximum Height	20.18 In (512.57 mm)
Width	14.25 In (361.95 mm)
Depth	0.7 In (17.78 mm)
Tightening torque	20.36 Lbf.In (2.3 N.m) cover

### Ordering and shipping details

Category	00001 - QO 1PH LC,12-42 CKT,NEMA1
Discount Schedule	DE3A
GTIN	00785901746010
Nbr. of units in pkg.	1
Package weight(Lbs)	6.6 Lb(US) (2.99 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.40 In (3.556 cm)
Package 1 width	14.60 In (37.084 cm)
Package 1 Length	21.40 In (54.356 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	162

Package 2 Weight	1051.00 Lb(US) (476.725 kg)
Package 2 Height	39.50 In (100.33 cm)
Package 2 width	40.00 In (101.6 cm)
Package 2 Length	48.00 In (121.92 cm)

**Offer Sustainability**

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

**Contractual warranty**

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**