

Product data sheet

Characteristics

QOGP3P6036

Generator panel, QO, 1 phase, 18 spaces, 36 circuits, 60A main breaker, NEMA1, cover with door, UL



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 495.00 USD

Main

| | |
|---------------------------|-------|
| Range of product | QO |
| Product or component type | Panel |

Complementary

| | |
|-----------------------------------|------------------------------------|
| Load center type | Main breaker |
| Line Rated Current | 60 A |
| Number of spaces | 18 |
| Short-circuit current | 10 KA |
| Number of circuits | 36 |
| Number of tandem circuit breakers | 18 |
| Phase | 1 phase |
| [Ue] rated operational voltage | 120/240 V AC |
| AWG gauge | AWG 8...AWG 2 aluminium/copper |
| Electrical connection | Lugs |
| Device composition | Grounding bar (ordered separately) |
| Electrical connection | Lugs |
| Wiring configuration | 3-wire |
| Box number | 6 |
| Maximum Height | 17.91 In (455 mm) |
| Maximum Width | 14.25 In (362 mm) |
| Maximum Depth | 3.74 In (95 mm) |

Environment

| | |
|---------------------------------------|---------------------------------|
| NEMA degree of protection | NEMA 1 indoor generator |
| Ambient air temperature for operation | 23 °F (-5 °C) 104 °F (40 °C) |
| Product certifications | UL Listed CSA |

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 00145 - HOM LC&CVR,12-42CKT NEMA3R |
| Discount Schedule | DE3C |
| GTIN | 00785901377252 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 20.58 Lb(US) (9.33 kg) |
| Returnability | No |
| Country of origin | US |

Packing Units

| | |
|------------------|----------------------|
| Package 1 Height | 5.50 In (13.970 cm) |
| Package 1 width | 16.00 In (40.640 cm) |
| Package 1 Length | 20.40 In (51.816 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| RECh free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |

| | |
|-----------------------|-----------------------|
| Product Life Status : | Commercialised |
|-----------------------|-----------------------|