

Product data sheet

Characteristics

RC2040M200S

All-In-One Ringless OH/UG200ASurface



by Schneider Electric

Product availability: Stock - Normally stocked in distribution facility

Price*: 1832.00 USD

Main

Product or component type	All-In-One
Range of product	QO
Meter socket type	Ringless
Hub type	A

Complementary


Line Rated Current	200 A
Short-circuit current	22 kA
Device mounting	Surface
Number of spaces	20
Number of circuits	40
Number of tandem circuit breakers	20
Electrical connection	Lugs line side Lugs service ground
AWG gauge	AWG 6...350 kcmil (aluminium/copper) line side AWG 8...AWG 2/0 (aluminium/copper) service ground
Device composition	Service disconnect (factory installed)
Service disconnect rated current	200 A
Branch circuit breaker rated current	200 A
Service feed location	OH outdoor UG
Bypass type	No bypass

Ordering and shipping details

Category	00148 - HOMELINE CSED DEVICES
Discount Schedule	DE3A
GTIN	00785901894414
Nbr. of units in pkg.	1
Package weight(Lbs)	61

Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0944 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	-----------------------