



### Main

Range	Odace
Product or component type	Switch
Device presentation	Mechanism with plastic fixing frame
Device application	Control
Type of packing	Paint cover
Quantity per set	Set of 10

### Complementary

Device mounting	Flush
Switch function	Intermediate
Number of rocker	1
Actuator	Rocker
Fixing mode	By screws
Colour tint	White (RAL 9003)
Surface finish	Glossy
Provided equipment	Internal power connection
Rated current	10 AX - 250 V AC 50 Hz
Load type	Load for energy saving lamps with ballast 100 W
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un with $\cos \varphi = 0.3$
Service life in cycles	20000 cycles @ ON and OFF at rated voltage with $\cos \varphi = 0.6$
Electrical durability	20000 cycles @ ON and OFF at rated voltage with $\cos \varphi = 0.6$
Number of terminals	4 screwless terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> stranded cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> flexible cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> rigid cable(s)
Wire stripping length	12 mm
Local signalling	Lightable
Material	Centre plate : thermoplastic ABS-UV stabilised Support frame : PBT (polybutylene terephthalate) GF30 Casing : PC (polycarbonate) GF10 FR
Height	71 mm
Width	71 mm
Depth	33.6 mm
Embedding depth	18.75 mm
Product weight	0.04 kg

## Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	2006/95/EEC EN 60669-1
Product certifications	NF N LCIE : NF 604950 Aenor : 030/2237 LCIE : CCA-FR_598285B
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1148 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**