



Main

Range	Odace
Aesthetic name	Touch
Product or component type	Cover frame
Number of gangs	1 gang
Type of frame	Single
Type of packing	Flow-pack
Quantity per set	Set of 10
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Fixing mode	Clip-in
Colour tint	White and metal martele aluminium (RAL 9003)
Surface finish	Glossy and martele
Material	Aluminium PC (polycarbonate) decorative frame
Height	85 mm
Width	85 mm
Depth	10 mm
Product weight	0.01298 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	2006/95/EEC EN 60669-1 NF C 61-314 NBN C 61-112-1 UNE 20315-1-1
Product certifications	NF N Aenor : 030/2205 LCIE : NF 603415A LCIE : CCA-FR_598285B
IK degree of protection	IK04
IP degree of protection	IP21D

Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1148 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months 18 months
-----------------	---------------------

Product Life Status : **Commercialised**