



Main

Range	Odace
Aesthetic name	Touch
Product or component type	Cover frame
Distance between centers	71 mm
Number of gangs	2 gangs
Installation direction	Horizontal/Vertical
Type of frame	Double
Type of packing	Flow-pack
Quantity per set	Set of 5
Sale per indivisible quantity	1

Complementary

Device mounting	Flush
Fixing mode	Clip-in
Colour tint	White and wood nature (RAL 9003)
Surface finish	Glossy and matt
Material	Wood PC (polycarbonate) decorative frame
Height	85 mm
Width	156 mm
Depth	10 mm
Product weight	0.02176 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	2006/95/EEC EN 60669-1 NF C 61-314 NBN C 61-112-1 UNE 20315-1-1
Product certifications	NF N Aenor : 030/2205 LCIE : NF 603415A
IK degree of protection	IK04
IP degree of protection	IP21D

Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1148 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months 18 months
-----------------	---------------------

Product Life Status : **Commercialised**