



Main

Range	Odace
Aesthetic name	Styl
Product or component type	Socket-outlet
Device presentation	Complete socket-outlet
Socket number	1
Type of packing	Paint cover
Quantity per set	Set of 10
Number of terminals	3

Complementary

Device mounting	Flush
Outlet poles configuration	2P + E with shutters
Outlet standard description	Side earth
Outlet standard	German
Fixing mode	By screws
Colour tint	White (RAL 9003)
Surface finish	Glossy
Rated current	16 A - 250 V AC 50 Hz
Service life in cycles	5000 cycles
Electrical durability	5000 cycles
Connections - terminals	Screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 4 mm ² rigid cable(s) 1 x 1.5...2 x 4 mm ² stranded cable(s) 1 x 1.5...2 x 4 mm ² flexible cable(s)
Wire stripping length	12 mm
Material	ASA + PC mechanism cover PBT (polybutylene terephthalate) GF30 support frame PC (polycarbonate) GF10 FR casing
Height	71 mm
Width	71 mm
Depth	45.4 mm
Embedding depth	29.5 mm
Product weight	0.061 kg

Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	UNE 20315-1-1 UNE 20315-1-2
Product certifications	N Aenor : 030/2210
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months 18 months
-----------------	---------------------

Product Life Status : **Commercialised**