



Main

Range	Odace
Product or component type	Switch + push-button
Device presentation	Mechanism with plastic fixing frame
Device application	Control
Quantity per set	Set of 1
Condition of use	Indoor

Complementary

Device mounting	Flush
Switch function	1-pole 2-way
Number of rocker	2
Actuator	Rocker and push-button
Fixing mode	By screws
Colour tint	White (RAL 9003)
Surface finish	Glossy
Rated current	10 AX - 250 V AC 50/60 Hz
Load type	Load for energy saving lamps with ballast 100 W
Minimum load breaking capacity	200 operations 1.25 I _n and 1.1 U _n with cos φ = 0.3
Service life in cycles	20000 cycles @ ON and OFF at rated voltage with cos φ = 0.6
Electrical durability	20000 cycles @ ON and OFF at rated voltage with cos φ = 0.6
Number of terminals	6 screwless terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² stranded cable(s) 1 x 1.5...2 x 2.5 mm ² flexible cable(s) 1 x 1.5...2 x 2.5 mm ² rigid cable(s)
Wire stripping length	12 mm
Local signalling	Lightable
Material	Centre plate : thermoplastic ABS-UV stabilised Support frame : PBT (polybutylene terephthalate) GF30 Casing : PC (polycarbonate) GF10 FR
Height	71 mm
Width	71 mm
Depth	33.6 mm
Embedding depth	18.75 mm
Product weight	0.04 kg

Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	2006/95/EEC EN 60669-1
Product certifications	NF LCIE : NF 619318A
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Petrol Liquid soap Window-cleaning fluid Oil Bleach Ammonia Acetone Alcohol UV resistant
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**