



Main

Range	Odace
Product or component type	SAT single shield
Device presentation	Mechanism with plastic fixing frame
Type of packing	Paint cover
Quantity per set	Set of 5

Complementary

Device mounting	Flush
SAT connector	F type
Path attenuation	1.5 dB for SAT signal @ 950...2150 MHz
Fixing mode	By screws
Colour tint	Aluminium
Connections - terminals	Screw
Shape of screw head	Pozidriv No 1
Wire stripping length	8 mm
Type of cable	Coaxial
Cable outer diameter	7 mm
Material	PBT (polybutylene terephthalate) GF30 support frame Thermoplastic ABS-UV stabilised centre plate Zinc alloy casing
Height	71 mm
Width	71 mm
Depth	34.1 mm
Embedding depth	18.1 mm
Product weight	0.042 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 50083-4 2006/95/EC
IK degree of protection	IK04
IP degree of protection	IP21D

Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**