



### Main

Range of product	Odace
Product or component type	Time delay switch
Device presentation	Mechanism with plastic fixing frame
Type of packing	Paint cover

### Complementary

Wiring device mounting	Flush
Provided equipment	Supplied with claws
Fixing mode	By claws By screws
Colour tint	Aluminium
Time delay	2 s...12 min
Load type	1840 W for 230 V AC halogen lamp 1840 W for heater 1840 VA for low voltage halogen lamp with ferromagnetic transformer 1840 W for 230 V AC fluorescent lamp with conventional ballast 1840 VA for low voltage halogen lamp with electronic transformer 500 VA for 230 V AC fluocompact lamp 690 W for ventilator 1840 W for 230 V AC incandescent lamp
Rated current	8 A - 230 V AC 50 Hz
Protection type	Electronic fuse protection
Connected auxiliaries	Maximum 25 auxiliary push-buttons without light indication Maximum 10 auxiliary push-buttons with light indication
Number of terminals	5 screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> solid cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> stranded cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> flexible cable(s)
Wire stripping length	8 mm
Status LED	Blue LED for load OFF indication
Material	PBT (polybutylene terephthalate) GF30 support frame Thermoplastic ABS-UV stabilised centre plate PA (polyamide) 6 GF20 FR casing
Height	71 mm
Width	71 mm
Depth	47.5 mm
Embedding depth	33 mm
Product weight	0.07 kg

## Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	2004/108/EC 2006/95/EEC EN 60669-1
Product certifications	NF N Cenelec : CCA-FI_2319
IK degree of protection	IK04
IP degree of protection	IP40

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1409 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**