



Main

Range	Odace
Range of product	Odace
Aesthetic name	Touch
Product or component type	Cover frame
Number of gangs	1 gang
Type of frame	Single
Quantity per set	Set of 1
Sale per indivisible quantity	1
Main colour tint	Anthracite
Condition of use	Indoor
Main material	PC (polycarbonate)

Complementary

Device mounting	Flush
Number of gangs	1 gang
Fixing mode	Clip-in
Colour tint	Anthracite and stone ardoise
Surface finish	Glossy and true stone
Material	Stone veneer PC (polycarbonate) decorative frame
Height	85 mm
Width	85 mm
Depth	10 mm
Product weight	0.0206 kg
Targeted channel	Do it yourself

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	2006/95/EEC NF C 61-314 UNE 20315-1-1 EN 60669-1
Product certifications	NF N Aenor : 030/2205 LCIE : NF 603415A
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Oil Window-cleaning fluid Liquid soap Ammonia Bleach UV resistant Petrol Alcohol
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1440 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**