



Main

Range	Odace
Range of product	Odace
Aesthetic name	Touch
Product or component type	Cover frame
Distance between centers	71 mm
Number of gangs	2 gangs
Installation direction	Horizontal/Vertical
Type of frame	Double
Quantity per set	Set of 1
Sale per indivisible quantity	1
Main colour tint	Anthracite
Condition of use	Indoor
Main material	PC (polycarbonate)


Complementary

Device mounting	Flush
Number of gangs	2 gangs horizontal / vertical 71 mm
Fixing mode	Clip-in
Colour tint	Anthracite and metal brushed bronze
Surface finish	Glossy and brushed
Material	Aluminium PC (polycarbonate) decorative frame
Height	85 mm
Width	156 mm
Depth	10 mm
Product weight	0.02176 kg
Targeted channel	Do it yourself

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 60669-1 2006/95/EEC NF C 61-314 UNE 20315-1-1
Product certifications	NF N Aenor : 030/2205 LCIE : NF 603415A
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone UV resistant Liquid soap Window-cleaning fluid Ammonia Petrol Bleach Alcohol Oil
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1440 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**