

Main

Range of product	Orion
Range	Orion
Aesthetic name	Orion Essence
Product or component type	Blind cover

Complementary

Device mounting	Flush
Fixing mode	Clip-in
Colour tint	Horizon gold (Pantone 8381C)
Surface finish	Matt
Surface treatment	Painted
Type of packing	Flow-pack
Quantity per set	Set of 20
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised for decorative frame
Height	127.5 mm
Width	120 mm
Depth	7.9 mm
Product weight	0.0331 kg

Environment

IK degree of protection	IK07
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid Hydrogen peroxide (H2O2)
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**