

Main

Range of product	Orion
Range	Orion
Aesthetic name	Orion materials aluminium
Product or component type	Cover frame

Complementary

Device mounting	Flush
Number of gangs	1 gang
Number of modules	6 modules
Fixing mode	Clip-in
Colour tint	Graphite (RAL 7021) Aluminium galaxy black (Pantone Cool Gray 11C)
Surface finish	Metallic
Surface treatment	Metallic
Type of packing	Blister
Quantity per set	Set of 10
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised for decorative frame Metal
Height	127.5 mm
Width	120 mm
Depth	8.3 mm
Product weight	0.031 kg

Environment

IK degree of protection	IK07
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid Hydrogen peroxide (H2O2)
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**