

### Main

Range of product	Orion
Range	Orion
Aesthetic name	Orion Essence
Product or component type	Cover frame

### Complementary

Device mounting	Flush
Provided equipment	Fixing frame
Number of gangs	1 gang
Number of modules	3 modules
Fixing mode	Clip-in
Colour tint	Black
Surface finish	Glossy
Surface treatment	Untreated
Type of packing	Flow-pack
Quantity per set	Set of 30
Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised for decorative frame
Height	82.5 mm
Width	120 mm
Depth	19.5 mm
Product weight	0.0389 kg

## Environment

IK degree of protection	IK07
IP degree of protection	IP21D
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid Hydrogen peroxide (H2O2)
Environmental health and issues	Halogen free

Product Life Status : **Commercialised**