

# SC2040M200PS

## ALL-IN-ONE RING OH/UG SURFACE 200A SOLAR



Product availability: Stock - Normally stocked in distribution facility

Price\*: 1671.00 USD

### Main

Product or component type	All-In-One
Range of product	Homeline
Meter socket type	Ringed
Hub type	A

### Complementary

Line Rated Current	200 A
Short-circuit current	22 kA
Number of spaces	20
Number of circuits	40
Number of tandem circuit breakers	20
Electrical connection	Lugs line side Lugs service ground
AWG gauge	AWG 4...250 kcmil (aluminium/copper) line side AWG 14...AWG 2/0 (aluminium/copper) service ground
Service disconnect rated current	200 A
Branch circuit breaker rated current	200 A
Service feed location	OH UG
Bypass type	No bypass
Connections - terminals	Plug-on neutral
Colour of enclosure	Grey
Product compatibility	Solar ready
Width	21.54 in (547 mm)
Depth	5.79 in (147 mm)
Height	30.39 in (772 mm)

## Environment

NEMA degree of protection	NEMA 3R
---------------------------	---------

## Ordering and shipping details

Category	00148 - HOMELINE CSED DEVICES
Discount Schedule	DE3A
GTIN	00785901342267
Nbr. of units in pkg.	1
Package weight(Lbs)	53.450000000000003
Returnability	Y

## Offer Sustainability

RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric Declaration Of Conformity</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

Product Life Status : **Commercialised**