



Main

Range of product	Sedna
Range	Sedna
Device application	Control
Product or component type	Switch
Switch function	Double 2-way
Device presentation	Without frame
Rated current	10 AX - 250 V AC
Cover plate colour tint	Graphite
Connections - terminals	Screwless terminals

Complementary

Accessory / separate part type	Claw and screw for mechanism
Power range	2300 W
Wiring device mounting	Flush
Number of cables	2 x 2.5 mm ²
Cable stiffness	Flexible Rigid
Wire stripping length	13 mm
Material	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Fixing mode	Claws, span of claws working range : 51...70 mm Screws
Height	71 mm
Width	71 mm
Depth	37 mm
Projecting depth	12 mm
Product weight	0.08492 kg

Environment

Standards	IEC 60669-1
Quality labels	CE
Product certifications	GOST-R
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1715 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**