



Main

Range	Sedna
Product or component type	Card switch
Device application	Control
Device presentation	Without frame
Cover plate colour tint	Graphite

Complementary

Switch function	Hotel card switch
Range compatibility	Sedna key card switch
Power range	2300 W
Rated current	10 AX - 250 V AC
Connections - terminals	Screwless terminals
Number of cables	2 x 2.5 mm ²
Cable stiffness	Flexible Rigid
Wire stripping length	13 mm
Material	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Fixing mode	Claws 51...70 mm Screws, span of claws working range :
Height	75 mm
Width	71 mm
Depth	55 mm
Projecting depth	31 mm
Product weight	0.063563 kg

Environment

Quality labels	CE
Product certifications	GOST-R
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1715 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**