

### Main

Range of product	Sedna
Product or component type	Socket-outlet
Device presentation	Without frame
Outlet poles configuration	2P + E with shutters
Outlet standard description	Side earth
Outlet standard	Poland
Rated current	16 A - 250 V AC
Cover plate colour tint	Titanium
Connections - terminals	Screwless terminals
Market segment	Residential Small commercial

### Complementary

Wiring device mounting	Flush
Power range	3680 W
Number of cables	2 x 2.5 mm <sup>2</sup>
Cable stiffness	Flexible Rigid
Wire stripping length	13 mm
Material	PC
Surface finish	Glossy
Fixing mode	Screws 52...69 mm Claws, span of claws working range :
Height	71 mm
Width	71 mm
Depth	47.3 mm
Projecting depth	16 mm
Product weight	0.070563 kg

### Environment

Standards	IEC 60884-1
Product certifications	GOST-R
IP degree of protection	IP20

Product Life Status : **Commercialised**