



### Main

Range	Sedna
Product or component type	TV/R socket
Device application	Media device support
Device presentation	Mechanism with central plate
TV socket type	Intermediate socket (passage)
Device composition	Support ring
Cover plate colour tint	Graphite

### Complementary

TV connector	1 x male IEC 9.52 mm
Radio connector	1 x female IEC
Number of outputs	2
Through loss	4 dB
Attenuation	4 dB for TV signal for 5...862 MHz frequency 10 dB for R signal for 88...125 MHz frequency
Connections - terminals	Screw terminals
Material	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Marking	With imprint
Device mounting	Flush
Fixing mode	Claws, span of claws working range : 55...70 mm Screws
Height	70 mm
Width	64 mm
Depth	40 mm
Projecting depth	14.6 mm
Product weight	0.10253 kg

### Environment

Quality labels	CE
IP degree of protection	IP20
Environmental health and issues	Halogen free

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**