



Main

Range	Unica
Product or component type	USB charger
Device presentation	Mechanism

Complementary

Device application	Charger
Device mounting	Flush
Colour tint	White
Connector type	USB 2.0
[Ue] rated operational voltage	100...240 V AC 50/60 Hz
Maximum power consumption in W	0.1 W
Input power	7.5 W
Socket number	1
Integrated connection type	1 USB 2.0 port 5 V DC, maximum load current: 1 A
Material	ABS (acrylonitrile butadiene-styrene): centre plate PC (polycarbonate) GF10 FR: casing PC (polycarbonate) GF10 FR: internal cover
Protection type	Short-circuit protection
Number of terminals	2 screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1.5...2.5 mm ² for rigid cable(s) 1.5...2.5 mm ² for flexible cable(s) 1.5...2.5 mm ² for stranded cable(s)
Wire stripping length	8 Mm
Product compatibility	All devices fulfilling the EN 62684 standard
Fixing mode	Screws or claws
Type of packing	Blister
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C
Standards	WEEE directive 2002/96/EC 2004/108/EC ETSI EN 301 489-4 2006/95/EC EN 62684 EN 60950-1 EU directive 2002/95/EC
Height	45 Mm
Width	22.5 Mm
Depth	42 Mm
Embedding depth	30.8 Mm
Net weight	0.03 Kg

Environment

Electrical insulation class	Class II
Environmental characteristic	REACH Regulation (EC) No 1907/2006
IK degree of protection	IK04
IP degree of protection	IP20

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Product Life Status : **Commercialised**