



Main

Range of product	SM6
Technology type	Air insulated switchgear
Device short name	IM 375
Product or component type	Switch
Integral instant protection	12.5 KA 1 s
Network type	AC
Sensor type	VPIS
Number of cables	1 x 240 mm ² per phase (bottom)

Complementary

Bus rated current	630 A 400 A 1250 A
Type of operator	CI1 manual
Net weight	120 Kg
Width	375 Mm

Environment

Standards	IEC 62271-100
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-40...70 °C
IP degree of protection	IP3x
Vibration resistance	0.5 gn horizontal class 2 0.4 gn vertical class 2
Operating altitude	<= 1000 m
Colour code	RAL 9003

Product Life Status : **Commercialised**