



### Overview

Model Name	APC Smart-UPS 750VA LCD RM 2U 120V with SmartConnect
Includes	CD with software , Documentation CD , Installation guide , Rack Mounting support rails , Smart UPS signalling RS-232 cable , USB cable
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Aruba , Bahamas , Barbados , Bermuda , Canada , Colombia , Costa Rica , Dominican Republic , Ecuador , El Salvador , Guatemala , Haiti , Honduras , Jamaica , Mexico , Nicaragua , Pakistan , Puerto Rico , Trinidad And Tobago , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

### Output

Output Power Capacity	500 Watts / 750 VA
Max Configurable Power (Watts)	500 Watts / 750 VA
Nominal Output Voltage	120V
Output Voltage Distortion	Less than 5%
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Other Output Voltages	110, 127V
	Line Interactive
Waveform Type	Sine wave
Output Connections	(6) NEMA 5-15R (Battery Backup)

### Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	8 feet (2,44 meters)
Input voltage range for main operations	82 - 144 V
Input voltage adjustable range for mains operation	75 - 154V
Other Input Voltages	110 , 127

### Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	3 hour(s)
Replacement Battery	APCRBC123
RBC Quantity	1

## Communications & Management

Interface Port(s)	RJ-45 Serial , SmartSlot , USB
Available SmartSlot&trade; Interface Quantity	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	--

## Surge Protection and Filtering

Surge energy rating	680 Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Physical

Maximum Height	3.39 inches (86.0 mm)
Maximum Width	17.0 inches (432.0 mm)
Maximum Depth	16.11 inches (409.0 mm)
Rack Height	2 U
Net Weight	39.03 lbs (17.7 kg)
Shipping Weight	49.93 lbs (22.65 kg)
Shipping Height	9.25 inches (235.0 mm)
Shipping Width	21.06 inches (535.0 mm)
Shipping Depth	22.44 inches (570.0 mm)
Color	Black
Units per Pallet	16.0

## Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)
Audible noise at 1 meter from surface of unit	41.000 dB
Online Thermal Dissipation	70.000 BTU/hr

## Conformance

Approvals	CSA , CSA C22.2 No. 107.1 , FCC Part 15 Class A , ICES-003 , UL 1778
Standard warranty	3 years repair or replace (excluding battery) and 2 year for battery
Equipment protection policy	Lifetime : \$150000

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs