

Overview

Model Name	APC Smart-UPS SRT 6000VA 208V Taiwan
Includes	CD with software
Standard Lead Time	Usually in Stock
Product Distribution	Taiwan

Output

Output Power Capacity	6000 Watts / 6000 VA
Max Configurable Power (Watts)	6000 Watts / 6000 VA
Nominal Output Voltage	208V
Output Voltage Distortion	Less than 2%
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Other Output Voltages	240V
Crest Factor	3 : 1
	Double Conversion Online
Waveform Type	Sine wave
Output Connections	(1) Hard Wire 3-wire (2PH + G) (Battery Backup)
Bypass	Internal Bypass (Automatic and Manual)

Input

Nominal Input Voltage	208V
Input Frequency	40 - 70 Hz (auto sensing)
Input Connections	Hard Wire 3-wire (2PH + G)
Input voltage range for main operations	160 - 275 V
Input voltage adjustable range for mains operation	100 - 275 (half load)V
Other Input Voltages	240

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	1.5 hour(s)
Replacement Battery	APCRBC140
RBC Quantity	1

Communications & Management

Interface Port(s)	RJ-45 10/100 Base-T
Available SmartSlot™ Interface Quantity	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	480 Joules
---------------------	------------

Physical

Maximum Height	432.0 mm
Maximum Width	174.0 mm
Maximum Depth	719.0 mm
Net Weight	61.23 kg
Shipping Weight	64.41 kg
Shipping Height	370.0 mm

Shipping Width	610.0 mm
Shipping Depth	960.0 mm
Color	Black
Units per Pallet	6.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	55.000 dB
Online Thermal Dissipation	1402.000 BTU/hr
Protection Class	IP 20

Conformance

Approvals	CSA C22.2 No.107.3-05
Standard warranty	3 years repair or replace (excluding battery) and 2 years for battery

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant